

# The only in the ear RF-receiver



## invisity 4 channels with remote control

invisity 4 channels with 4 programmable channels (within 7 MHz) is bundled with the invisity remote control to change the preset channels with programmable frequencies. The invisity programming set comprises the invisity programming unit (IPU), the software (Win) and a USB cable. The set allows you to program your invisity and your invisity remote control quickly, simply. On the invisity 4 channels you can read and edit frequencies, volumes, names, comments.



### Frequency ranges available invisity:

- S1 158.0000–164.0000
- S2 164.0000–170.8000
- HA 169.4000–176.0000
- S3 175.0000–182.0000
- S4 181.0000–188.0000
- N 214.0000–220.0000

invisity 4 channels is now available in 3 different sets to suit to your various requests:

### invisity single set



- 1 x invisity 4 channels + 1 x RC invisity
- 1 x IPU, with USB cable and software

in a custom made, waterproof safety case

### invisity 4 units set

The ready made set to be operational in any situation, made of  
4 x invisity 4 channels with 4 x RC invisity  
1 x IPU, with USB cable and software  
1 x box of 60 A10 batteries  
1 x box of 110 Cerumex filters  
and extra space for a transmitter

### The interrogator set

The ready made set is specially designed for interrogation and is  
proposed with 3 various types of discreet transmitters:

The invisity 4 units-set combined with a discreet transmitter,  
specially made for short range.

The set include:

4x invisity 4 channels with 4 x RC invisity  
1x IPU, with USB cable and software  
1x box of 60 A10 batteries  
1x box of 110 Cerumex filters  
+1 transmitter to choose

### Frequency ranges available microTX-S:

H 173.0000–185.0000  
J 185.0000–201.0000  
N 207.0000–217.0000

### Frequency ranges available

#### SmartLink/EasyLink:

H 169.4000–181.9000  
N 214.0000–220.0000



microTX-S



SmartLink



EasyLink



in a custom made, waterproof safety case

All these sets are also available with invisity Flex.

For further information, please contact your  
nearest agent or visit our webpage:

## CONTACT:

Phonak Communications AG  
Länggasse 17  
CH-3280 Murten  
Switzerland

Phone +41 (0) 26 672 96 72

Fax +41 (0) 26 672 96 77

[www.phonakcom.ch](http://www.phonakcom.ch)

[info@phonakcom.ch](mailto:info@phonakcom.ch)